

## Range Hoods with P-System



"Typically when installing a furniture-style range hood in a kitchen project, it's one of the last items to be installed. The P-system connectors allow us to construct and install a fastener-free final product. Additionally, the P-system connectors allow us to have accessibility to the initial connections of blower motor, ducting, and electrical as well as maintain access for homeowner maintenance down the road."

## Matt Moore, Owner, Matt Moore Designs, Jacksonville, FL



"The Lamello P-System works wonders for many range hood designs. It allows the hood to be built, but enables the front to be popped off, giving the hvac installer access to properly fit, elbow, and tape off the piping for the blower fan. This is a win for all parties involved! After properly connecting the piping, the hood front is simply snapped back on with Tensos giving flexibility in the future if access would be required again."

Chad Kramer, Owner of Retrotech Construction, Delano, MN

## How it works:



Lay out and machine P-System slots for top edge of front panel



Transfer marks from front access panel to upper unit



Transfer center line of slots to upper unit



Machine P-System slots in upper unit



Lay out location for Clamex P-14 slots



Machine slots in edge of hood frame uprights



Machine slots on back side of front access panel



Install Clamex connectors; male half on the access panel



Use Bisco connectors at top edge for alignment and positioning



Slide top of access panel into place



Hinge access panel down to bottom of frame



Use Clamex to secure or remove front access panel



## Lamello P-System tools, connectors & accessories





| Zeta P2 biscuit joiner                          | Art. No. |
|-------------------------------------------------|----------|
| In Systainer, with carbide cutter and drill jig | 1014025  |
| In Systainer, with diamond cutter and drill jig | 101402DS |



| Clamex P-14 | Art. No |
|-------------|---------|
| 80 pairs    | 145334  |
| 300 pairs   | 145346  |
| 1000 pairs  | 145356  |
|             |         |



| Zeta P2 cordless biscuit joiner, DP (diamond)    | Art. No. |
|--------------------------------------------------|----------|
| In Systainer, incl. 2 batteries<br>and charger   | 101801SD |
| In Systainer, without batteries, without charger | 101800SD |



| Clamex P-14/10 Medius | Art. No. |
|-----------------------|----------|
| 80 pairs              | 145370   |
| 300 pairs             | 145371   |



| P-System connector                              |          |
|-------------------------------------------------|----------|
| assortment professional                         | Art. No. |
| Includes: 80 pairs Clamex P-14,                 | 145314   |
| 80 pairs Tenso P-14 incl. clip, 60 pairs Clamex |          |
| P14/10 Medius, 20 pieces Bisco P-14,            |          |
| Tenso P-14/10 preload tool, Systainer II T-Loc  |          |
| incl. compartment dividers                      |          |



| Clamex P-10 | Art. No. |
|-------------|----------|
| 80 pairs    | 145372   |
| 300 pairs   | 145373   |
| 1000 pairs  | 145374   |
|             |          |



| assortment professional                         | Art. No. |
|-------------------------------------------------|----------|
| Includes: 80 pairs Clamex P-14,                 | 145314   |
| 80 pairs Tenso P-14 incl. clip, 60 pairs Clamex |          |
| P14/10 Medius, 20 pieces Bisco P-14,            |          |
| Tenso P-14/10 preload tool, Systainer II T-Loc  |          |
| incl. compartment dividers                      |          |
|                                                 |          |



| Clamex P-14/10 Flexus | Art. No. |
|-----------------------|----------|
| 80 pairs              | 145315   |
| 300 pairs             | 145316   |
| 1000 pairs            | 145317   |



| assortment basic                               | Art. No. |
|------------------------------------------------|----------|
| Includes: 120 pairs                            | 145312   |
| Clamex P-14, 30 pairs Clamex                   |          |
| P-14/10 Flexus, 30 pairs Clamex P-10,          |          |
| 80 pairs Tenso P-14 incl. clip,                |          |
| 30 pairs Tenso P-10 incl. clip                 |          |
| 20 pieces Bisco P-14, 20 pieces                |          |
| Bisco P-10, 80 pairs Divario P-18,             |          |
| Divario installation tool/drill/marking gauge, | Clamex,  |
|                                                |          |

P-System connector



| Bisco P-14  | Art. No. |
|-------------|----------|
| 80 pieces   | 145301   |
| 300 pieces  | 145302   |
| 1000 pieces | 145303   |



| Clamex P-14, 30 pairs Clamex                           |
|--------------------------------------------------------|
| P-14/10 Flexus, 30 pairs Clamex P-10,                  |
| 80 pairs Tenso P-14 incl. clip,                        |
| 30 pairs Tenso P-10 incl. clip                         |
| 20 pieces Bisco P-14, 20 pieces                        |
| Bisco P-10, 80 pairs Divario P-18,                     |
| Divario installation tool/drill/marking gauge, Clamex, |
| P installation tool, Tenso P-14/10 preload tool,       |
| Sortainer T-loc                                        |
|                                                        |



| Bisco P-10 | Art. No |
|------------|---------|
| 80 pieces  | 145304  |
| 300 pieces | 145305  |



| Divario P-18 Starter Set          | Art. No. |
|-----------------------------------|----------|
| In Systainer3, includes: Divario  | 145551   |
| P-18, 80 pairs, drill, metal      |          |
| marking its and installation tool |          |



| Divario P-18 | Art. No. |
|--------------|----------|
| 80 pairs     | 145550   |
| 300 pairs    | 145560   |
| 1000 pairs   | 145570   |





| Tenso P-14                  | Art. No. |
|-----------------------------|----------|
| 30 pairs                    | 145415   |
| 30 pairs, with preload clip | 1454155  |
| 300 pairs                   | 145425   |
| 000 pairs                   | 145435   |



| Art. No. |
|----------|
| 145426   |
| 145436   |
|          |



| enso P-10                    | Art. No. |
|------------------------------|----------|
| 0 pairs, with preload clip   | 145418   |
| 00 pairs, with preload clip  | 145428   |
| 000 pairs, with preload clip | 145438   |
| 000 pairs, with preload clip |          |

Your distribution partner: